



RIGID

MAX

MAX

RELION F

SOFT COUNTERS Polyester fabric backers with PU adhesive on both sides

PRODUCT **CHARACTERISTICS**

SHAPE RETENTION

WORKABILITY

RIGIDITY

SOFT

MIN

PRODUCT DESCRIPTION


RELION F is the latest soft development for RELION counter family, produced by copolymer extrusion. It provides very flexible and elastic properties. It has easy workability and special moulding properties: high resiliency and excellent shape reproduction and retention. It is suitable for all types of footwear. It has also been used as an insole in orthopedic footwear.

TECHNICAL DATA

RELION F

Thickness* (mm)

Cutting direction



* All thickness values have a natural variation of ± 0,05mm

INSTRUCTIONS OF USE

Relion F can be used both by preheating the material before insertion both placing the cold material between lining and upper.

1) USE WITH PREHEATING

The counter stretched can be warmed to 70-80°C on a Teflon's hot plate that allows optimum control of the temperature. Other heat sources can also be used as ovens, lamps and hot steam.

The counter so heated softens quickly. As the special polymer compound is not sticky fingers, the operator can manually enter the counter between upper and lining without any problem. The counter is then glued and formed with a backpart moulding machine. What optimum working conditions suggest:

- Temperature of the form: from 110°C to 130°C depending on the nature of lining and upper used (natural or synthetic).

- Minimum effective interface temperature: 100°C
- Contact time: from 10 to 15 seconds (high operating temperatures allow contact times reduced and vice versa).

2) USE WITHOUT PREHEATING

The material is placed between liner and upper and formed using a backpart moulding machine. We recommend the following working conditions:

- Temperature of the shape: 140-150°C depending on the nature of lining and upper used (natural or synthetic).
- Minimum effective interface temperature: 100°C
- Contact time: from 10 to 15 seconds (high operating temperatures allow contact times reduced and vice versa).



RECOMMENDED FOR

In case of backpart moulding machine with two positions, the subsequent cold stabilization allows to obtain a counter perfectly shaped.

ATTENTION: the application of solvent glue can affect the adhesive present on the sheet, causing detachment.





RECYCLABLE. SCRAPS REUSED IN THE PRODUCTION PROCESS.

EM 01 11/11/2020

Sneakers **Boots Point shoes** Décolleté shoes **Casual shoes**

This Statement has been released on request, on the basis of our best actual knowledge

TECNOGI S.p.A. - Via del Vallo 7 - 28071 Borgolavezzaro (NO) - Italy www.tecnogi.com export@tecnogi.com